



MKH 50-P48

Quick Guide

Kurzanleitung

Guide de démarrage rapide

Guida rapida

Instrucciones resumidas

Instruções resumidas

Beknopte gebruiksaanwijzing

Krótką instrukcja obsługi

Snabbguide

Kort vejledning

Pikaohje

Γρήγορος οδηγός

Kisa Kilavuz

Краткая инструкция

快速指南

快速使用指南

クイックガイド

퀵 가이드

SENNHEISER



www.sennheiser.com/documentation




www.sennheiser.com/download

Sennheiser electronic SE & Co. KG


Am Labor 1, 30900 Wedemark, Germany
www.sennheiser.com

Publ. 07/26, 583989/A04


In the box



MZQ 40




MZS 40



MZW 41




Overview



- 1 switch for preattenuation
- 2 switch for roll-off-filter
- 3 XLR-3 connector



Adjusting



Setup



MZW 41




MZQ 40

5/8"




attenuation at 40 Hz: approx. 20 dB




MZS 40

5/8"





* not included

Power supply and connections




Cleaning




Accessories


MZS 20-1*



MZS 20-1*



MZH 20-1*





* not included

Specifications

Pick-up pattern	super-cardioid
Frequency response	40 – 20,000 Hz
Sensitivity (free field, no load, 1 kHz)	25 (8) mV/Pa ±1 dB
Max. SPL	134 (142) dB / 1 kHz
Equivalent noise level	
A-weighted	12 (18) dB(A)
CCIR-weighted	21 (27) dB
Nominal impedance	150 Ω
Min. terminating impedance	1 kΩ
Phantom powering	48 V ± 4 V
Current consumption	2 mA
Dimension	∅ 25 x 153 mm
Weight	approx. 100 g

Values in () with attenuator switched on (–10 dB)

Polar pattern and frequency response



..... Effect of switchable roll-off filter

